

# MSAK810



**Brand:** Dino-Lite  
**Product Code:** MSAK810

## Short Description

Flexible extension arm

## Description

The MSAK810 adjustable flex arm which can be attached to the pole of a RK-06A/RK-06AE/RK-06F for additional hands free viewing angles with the Dino-Lite. The arm has a maximum of 30cm reach, and can be bent and twisted to attain your desired viewing positions.

The MSAK810 is a great addition to a RK-06A/RK-06AE/RK-06F allowing an in-depth visual inspection with multiple Dino-Lite's.

## Specification

|                  |                        |
|------------------|------------------------|
| Compatibility    |                        |
| Compatible with: | All Dino-Lite models   |
| Housing          |                        |
| Dimensions       | 35.5cm (W) x 3.1cm (L) |
| Weight           | 181 g                  |
| Features         |                        |
| ESD safe         | No                     |
| Information      |                        |
| Package contents | Stand, HD-P1 holder    |

|                      |                           |
|----------------------|---------------------------|
| Warranty information | 2 years European warranty |
| Accessory range:     | Professional stands       |
| Price range          | €50,00 - €150,00          |

## Product Gallery

