Dino-Lite Europe - Phone: - Email:

AM7115MZTL - EDGE

Código del producto: AM7115MZTL



Short Description

5 Megapixel resolution Robust metal housing 10-140x magnification Long working distance Flexible LED Control (FLC)

Descripción

With the use of the latest, cutting-edge optics, a brand new 5 megapixel sensor and several special features such as Flexible LED Control (FLC) and full aluminum body, the Dino-Lite AM7115MZTL is a marvel of technology and the best choice for the high-demanding professional. The Dino-Lite AM7115MZTL offers superb image quality and color reproduction in a robust, compact and appealing housing.











The AM7115MZTL is part of the Long Working Distance (LWD) range and with its Long Working Distance and magnification range from 10 - 140x, it is suitable for a wide range of applications where extra distance to the object or a larger field of view is required.

The extra working distance and larger field of view make this model an ideal solution for tasks such as repair, rework or assembly or for working with bulky or fragile objects that cannot be touched. Because of the built-in polarization filter this model is ideal when working with shiny or reflective objects such as metal, plastic, glass, jewelry, electronics, etc.

The main features of the AM7115MZTL are:

- 5 Megapixel Edge sensor
- Long Working Distance (LWD)
- 10-140x magnification
- Integrated polarizer
- Aluminum housing
- Flexible LED Control (FLC)
- Extensive measurement functions
- Calibration
- Exchangeable front caps
- And more...

Working distance/field of view/depth of field

MAGNIFICATI WORKING FIELD OF FIELD OF DEPTH OF ON RATE DISTANCE* VIEW(X) VIEW(Y) FIELD

Listed values * Without front Unit = mm

may differ cap

slightly

| 10 | 234.5 | 39.0 | 31.2 | 12 |
|-----|-------|------|------|------|
| 20 | 112.5 | 19.5 | 15.6 | 4.5 |
| 30 | 72.5 | 13.0 | 10.4 | 3.1 |
| 40 | 54.5 | 9.8 | 7.8 | 1.8 |
| 50 | 43.5 | 7.8 | 6.2 | 1.2 |
| 60 | 37.5 | 6.5 | 5.2 | 0.9 |
| 70 | 33.7 | 5.6 | 4.5 | 0.6 |
| 80 | 31.3 | 4.9 | 3.9 | 0.5 |
| 90 | 29.9 | 4.3 | 3.5 | 0.37 |
| 100 | 29.2 | 3.9 | 3.1 | 0.28 |
| 110 | 29.1 | 3.5 | 2.8 | 0.22 |
| 120 | 29.3 | 3.3 | 2.6 | 0.17 |
| 130 | 29.8 | 3.0 | 2.4 | 0.12 |
| 140 | 30.5 | 2.8 | 2.2 | 0.09 |
| | | | | |

Especificación

| Lighting | | | | |
|-------------------------|---|--|--|--|
| Light/ LED type | White | | | |
| Number of LEDs | 8 | | | |
| LED on/off switchable: | Yes | | | |
| Infrared filter | IR cut-filter >650 nm | | | |
| Diffuser available | Yes (N3C-D included) | | | |
| Emission filter | No | | | |
| Polarizer | Yes, linear | | | |
| Optics | | | | |
| Magnification | $10x \sim 140x$ | | | |
| Macro zoom | No | | | |
| Working distance | Long | | | |
| Lens type | Glass with anti-reflection coating | | | |
| Sensor | | | | |
| Sensor type | CMOS | | | |
| Resolution | 5.0 Megapixel (2592x1944) | | | |
| Maximum frame rate | 30 fps | | | |
| Compatibility | | | | |
| Interface | USB 2.0 | | | |
| Operating system | Windows 7, 8, 10 & 11, MacOS 10.9 and up | | | |
| Software | DinoCapture 2.0 (Windows), DinoXcope (Mac | | | |
| | OS) | | | |
| Supported image formats | BMP, GIF, PNG, JPG, TIF, RAS, PNM, TGA, | | | |
| (Windows) | PCX, MNG, WBMP, JP2, JPC, PGX | | | |
| Supported video formats | WMV, FLV, SWF | | | |
| (Windows) | | | | |

| Supported image formats (MacOS) | JPEG, PNG | | | |
|---------------------------------|---|--|--|--|
| Supported video formats | MOV (max 1.3MP) | | | |
| (MacOS) | | | | |
| Imaging standards | DirectShow, UVC | | | |
| Wifi | Wireless-ready, requires the WF-10 WiFi streamer | | | |
| | (optional) | | | |
| Housing | | | | |
| Housing material | Metal housing | | | |
| Magnification lock | Yes | | | |
| Dimensions | 10.5cm (L) x 3.2cm (D) | | | |
| Weight | 135gr | | | |
| Cable length | 1.8m | | | |
| Features | | | | |
| Special feature | Flexible LED Control (FLC) | | | |
| Measurement | Yes | | | |
| Calibration | Yes | | | |
| Microtouch sensor | Yes | | | |
| ESD safe | Yes | | | |
| Information | | | | |
| Package contents | Microscope, carry pouch, software CD, calibration | | | |
| | target, user manual, N3C-O- Open cap, N3C-C- | | | |
| | Closed cap, N3C-D- diffuser cap, N3C-E- | | | |
| | extension cap, N3C-L- Long cap, N3C-S- Side | | | |
| | light cap | | | |
| Warranty information | 2 years European warranty | | | |
| Regulatory approval | CE, FCC, ROHS | | | |
| Price range | €900,00 - €1100,00 | | | |

Product Gallery











