

AM4115TL - EDGE



Marca:

Código del producto: AM4115TL

Short Description

1.3 Megapixel resolution

Versatility due to exchangeable caps

10-140x magnification

Long working distance

Descripción

The wide range of magnification (10-140x), the large field of view and working distance of up to 23 cm makes the AM4115TL the ideal solution for all situations where a longer distance between the microscope and the object is required or when it is needed to work under the microscope (repair, rework and assembly tasks etc.)



USB 2.0



Measurement
functionality



Continuous
~10x - 140x



Magnification
lock



1.3 megapixel
1280 x 1024



8 White LEDs
switchable



Long working
distance



Exchangeable
cap

Working distance/field of view/depth of field

MAGNIFICATION RATE	WORKING DISTANCE*	FIELD OF VIEW(X)	FIELD OF VIEW(Y)	DEPTH OF FIELD
Listed values may differ slightly	* With front cap			Unit = mm

10	227	39.0	31.2	12
20	105	19.5	15.6	4.5
30	65	13.0	10.4	3.1
40	47	9.8	7.8	1.8
50	36	7.8	6.2	1.2
60	30	6.5	5.2	0.9
70	26.2	5.6	4.5	0.6
80	23.8	4.9	3.9	0.5
90	22.4	4.3	3.5	0.37
100	21.7	3.9	3.1	0.28
110	21.6	3.5	2.8	0.22
120	21.8	3.3	2.6	0.17
130	22.3	3.0	2.4	0.12
140	23	2.8	2.2	0.09

Especificación

Lighting	
Light/ LED type	White
Number of LEDs	8
LED on/off switchable:	Yes
Infrared filter	IR cut-filter >650 nm
Diffuser available	Yes (N3C-D included)
Emission filter	No
Polarizer	No
Optics	
Magnification	10x ~ 140x
Macro zoom	No
Working distance	Long
Lens type	Glass with anti-reflection coating
Sensor	
Sensor type	CMOS
Resolution	1.3 Megapixel (1280x1024)
Maximum frame rate	30 fps
Compatibility	
Interface	USB 2.0

Operating system	Windows 7, 8, 10 & 11, MacOS 10.9 and up
Software	DinoCapture 2.0 (Windows), DinoXcope (Mac OS)
Supported image formats (Windows)	BMP, GIF, PNG, JPG, TIF, RAS, PNM, TGA, PCX, MNG, WBMP, JP2, JPC, PGX
Supported video formats (Windows)	WMV, FLV, SWF
Supported image formats (MacOS)	JPEG, PNG
Supported video formats (MacOS)	MOV
Imaging standards	DirectShow, UVC
Wifi	Wireless-ready, requires the WF-10 WiFi streamer (optional)
Housing	
Housing material	Composite/ plastic housing
Magnification lock	Yes
Dimensions	10.5cm (L) x 3.2cm (D)
Weight	105g
Cable length	1.8m
Features	
Special feature	No
Measurement	Yes
Calibration	Yes
Microtouch sensor	Yes
ESD safe	No
Information	
Package contents	Microscope, carry pouch, software CD, calibration target, user manual, N3C-O- Open cap, N3C-C- Closed cap, N3C-D- diffuser cap, N3C-E- Extension cap, N3C-L- Long cap, N3C-S- Side light cap
Warranty information	2 years European warranty
Regulatory approval	CE, FCC, ROHS
Price range	€500,00 - €700,00

Product Gallery

