Dino-Lite Europe - Phone: - Email:

MSAK810



Código del producto: MSAK810

Short Description

Flexible extension arm

Descripción

The MSAK810 adjustable flex arm which can be attached to the pole of a RK-06A/RK-06AE/RK-06F for additional hands free viewing angles with the Dino-Lite. The arm has a maximum of 30cm reach, and can be bent and twisted to attain your desired viewing positions.

The MSAK810 is a great addition to a RK-06A/RK-06AE/RK-06F allowing an in-depth visual inspection with multiple Dino-Lite's.

Especificación

Compatibility	
Compatible with:	All Dino-Lite models
Housing	
Dimensions	35.5cm (W) x 3.1cm (L)
Weight	181 g
Features	
ESD safe	No
Information	
Package contents	Stand, HD-P1 holder

Warranty information	2 years European warranty
Accessory range:	Professional stands
Price range	€50,00 - €150,00

Product Gallery

