

# WF4115ZT



**Marca:**

**Código del producto:** WF4115ZT

## Short Description

1.3 Megapixel Edge sensor

20-220x magnification

Adjustable polarizer

Flexible LED Control (FLC)

Free iOS and Android App

## Descripción

The Dino-Lite WF4115ZT is a Wireless model that is part of the Universal series. Go from wireless to wired and back in an instant. Work wired via USB or work wireless with the attachable WF-20 Wireless adapter.



USB 2.0



1,3 Megapixels  
1280 x 1024



Adjustable  
~20x-220x



Polarizer  
anti-reflection



Measurement  
functionality



Flexible LED  
Control FLC



Magnification  
lock



Exchangeable  
cap



Standard working  
distance



The WF4115ZT is equipped with premium features such as Flexible LED control (FLC), integrated polarizer, extensive measurement functionality.

**The main features of the WF4115ZT are:**

- Completely wireless solution (including WF20)
- 20-220x magnification
- 1.3 Megapixel Edge sensor
- Extensive measurement functionality
- Adjustable polarizer
- Flexible LED Control (FLC)
- And more...

**Working distance/ field of view/ depth of field:**

MAGNIFICATION RATE	WORKING DISTANCE *	FIELD OF VIEW(X)	FIELD OF VIEW(Y)	DEPTH OF FIELD
<b>Listed values may differ slightly</b>	<b>* Without front cap</b>			<b>Unit = mm</b>
20	60.2	19.5	14.6	2.5
30	33.5	13.0	9.7	1.8
40	20.9	9.8	7.3	1.5
50	13.9	7.8	5.8	-
60	9.7	6.5	4.8	-
70	7.1	5.6	4.2	1.0
80	5.5	4.9	3.6	-
90	4.5	4.3	3.2	-
100	4.1	3.9	2.9	-
110	4.0	3.6	2.7	-
120	4.1	3.3	2.4	-
130	4.5	3.0	2.2	-
140	5.0	2.8	2.1	-
150	5.6	2.6	1.9	-
160	6.3	2.4	1.8	-
170	7.1	2.3	1.7	-

180	8.0	2.2	1.6	-
190	8.9	2.1	1.5	-
200	9.9	2.0	1.5	-
210	10.9	1.9	1.4	-
220	11.9	1.8	1.3	0.1

## Especificación

Lighting	
Light/ LED type	White
Number of LEDs	8
LED on/off switchable:	Yes
Infrared filter	IR cut-filter >650 nm
Diffuser available	Yes (N3C-D included)
Emission filter	No
Polarizer	Yes, linear
Optics	
Magnification	20x ~ 220x
Macro zoom	No
Working distance	Standard
Lens type	Glass with anti-reflection coating
Sensor	
Sensor type	CMOS
Resolution	1.3 Megapixel (1280x1024)
Maximum frame rate	30 fps
Compatibility	
Interface	USB 2.0
Operating system	Windows 7, 8, 10 & 11, MacOS 10.11.6 and up (cable only)
Software	DinoCapture 2.0 (Windows) cable + wireless, DinoXcope (Mac OS) cable only, DinoConnect wireless only
Supported image formats (Windows)	BMP, GIF, PNG, JPG, TIF, RAS, PNM, TGA, PCX, MNG, WBMP, JP2, JPC, PGX
Supported video formats (Windows)	WMV, FLV, SWF
Supported image formats (MacOS)	JPEG, PNG
Supported video formats (MacOS)	MOV

Imaging standards	DirectShow, UVC
Wifi	Yes
<b>Housing</b>	
Housing material	Composite/ plastic housing
Dimensions	11.4cm (L) x 3.3cm (D)
Weight	111g
Cable length	1.8m
<b>Features</b>	
Special feature	Flexible LED Control (FLC)
Measurement	Yes
Calibration	Yes
Microtouch sensor	Yes
ESD safe	No
<b>Information</b>	
Package contents	Microscope, WF-20, carry pouch, software CD, calibration target, user manual, N3C-O- Open cap, N3C-C- Closed cap, N3C-D- Diffuser cap, N3C-E- Extension cap, N3C-L- Long cap, N3C-S- Side light cap
Warranty information	2 years European warranty
Regulatory approval	CE, FCC, ROHS
Price range	€800,00 - €1000,00

## Product Gallery