

N3C-A



Marque: Dino-Lite
Code produit: N3C-A

Courte description

Coaxial Light Cap

Description

The N3C-A coaxial light cap is a useful accessory for the Dino-Lite Edge models from the Long Working Distance range. Especially difficult to inspect surfaces such as metal, plastics or glass benefit from this addition.

Inside the small and light front cap an ingenious mirroring system with a beam splitter has been integrated. The combination of coaxial lighting, a high sensitive camera and a magnification of up to 140 times makes it possible to visualize even the smallest scratches and dents on any surface. The coaxial lighting does also eliminate disturbing shadows making it easier to look inside small holes in the material you wish to check.

The NC3-A coaxial light cap is interchangeable with other caps from the Dino-Lite range. The optimum result can be achieved by using it in combination with a Dino-Lite Edge model from the Long Working Distance range (LWD).

Spécification

Compatibility

Compatible with:

All Long Working Distance Edge models
(AM4x15, AM4xx17, AM5216, AM5218,

	AM7x15, AM73xx15, type TL/ZTL)*
Housing	
Dimensions	18.5mm (H) x 30.3mm (D)
Weight	6 g
Features	
ESD safe	No
Information	
Package contents	N3C-A coaxial light cap, Quick start guide
Warranty information	2 years European warranty
Accessory range:	Light and control
Price range	€100,00 - €200,00
Note	*The working distance of Dino-Lite attached with N3C-A will be reduced by 5mm. Some magnification range of standard working distance models could thus be obscured from using. Standard working distance models may function with N3C-A at 225x or less than 50

Galerie du produit



