

AM4013MZT4

Marque: Dino-Lite
Code produit: AM4013MZT4



Courte description

1.3 Megapixel resolution
Robust metal housing
400-470x magnification
Polarizer (anti-reflection)

Description

The AM4013MZT4 with a high magnification of 400~470x reveals even the smallest details on all kinds of objects. The built-in, switchable polarizer makes the AM4013MZT4 the right choice for working with high glare materials such as jewelry, plastics and metals. The aluminum housing offers enhanced protection and durability and has the best look and feel.



USB 2.0



Measurement
functionality



Adjustable
~400x -470x



1,3 Megapixels
1280 x 1024



8 White LEDs
switchable



Metal
housing



Standard working
distance



Polarizer
anti-reflection

Working distance/field of view/depth of field

MAGNIFICATION RATE	WORKING DISTANCE	FIELD OF VIEW(X)	FIELD OF VIEW(Y)	DEPTH OF FIELD
Listed values may differ slightly				Unit = mm
430	-0.45	0.91	0.73	0.1
440	0.4	0.89	0.71	0.1
450	1.35	0.87	0.7	0.1
460	2.3	0.85	0.68	0.1
470	3.15	0.83	0.67	0.1

Spécification

Lighting	
Light/ LED type	White
Number of LEDs	8
LED on/off switchable:	Yes
Infrared filter	IR cut-filter >650 nm
Diffuser available	No
Emission filter	No
Polarizer	Yes, linear
Optics	
Magnification	400-470x
Macro zoom	No
Working distance	Standard
Lens type	Glass with anti-reflection coating
Sensor	
Sensor type	CMOS
Resolution	1.3 Megapixel (1280x1024)
Maximum frame rate	30 fps
Compatibility	
Interface	USB 2.0
Operating system	Windows 7,8,10 & 11, MacOS 10.9 and up

Included software	DinoCapture 2.0 (Windows), DinoXcope (Mac OS)
Supported image formats (Windows)	BMP, GIF, PNG, JPG, TIF, RAS, PNM, TGA, PCX, MNG, WBMP, JP2, JPC, PGX
Supported video formats (Windows)	WMV, FLV, SWF
Supported image formats (MacOS)	JPEG, PNG
Supported video formats (MacOS)	MOV
Imaging standards	DirectShow, UVC
Wifi	Wireless-ready, requires the WF-10 WiFi streamer (optional)
Housing	
Housing material	Metal housing
Magnification lock	No
Dimensions	10.5cm (L) x 3.2cm (D)
Weight	140g
Cable length	1.8m
Features	
Special feature	No
Measurement	Yes
Calibration	Yes
Microtouch sensor	Yes
ESD safe	Yes
Information	
Package contents	Microscope, carry pouch, software CD, calibration target, ZT-Z-CC1 cap closure, user manual
Warranty information	2 years European warranty
Regulatory approval	CE, FCC, ROHS
Price range	€600,00 - €800,00

Galerie du produit