

AF4915ZT



Merk: Dino-Lite
Productcode: AF4915ZT

Korte omschrijving

1.3 Megapixel Edge sensor
Extended Depth of Field (EDOF)
Extended Dynamic Range (EDR)
Flexible LED Control (FLC)
Automatic Magnification Reading (AMR)

Omschrijving

The Dino-Lite AF4915ZT is part of Universal series and connects to your device via USB. The AF4915ZT is Wireless-ready, but requires the (optional) WF-20 to make it a fully wireless solution.



USB 2.0



1,3 Megapixels
1280 x 1024



Adjustable
~20x-220x



Magnification
lock



Polarizer
anti-reflection



Measurement
functionality



Flexible LED
Control FLC



Standard working
distance




Automatic
Magnification
Reading (AMR)



Extended
Depth Of Field
EDOF



Extended
Dynamic
Range EDR



Exchangeable
cap

The AF4915ZT is equipped with premium features such as Extended Depth of Field (EDOF), Extended Dynamic Range (EDR), Flexible LED control (FLC), integrated polarizer, extensive measurement functionality and Automatic Magnification Reading (AMR) for measurement-intensive applications.

The main features of the AF4915ZT are:

- Wireless-ready, requires the WF-20 adapter (optional)
- 20-220x magnification
- 1.3 Megapixel Edge sensor
- Adjustable polarizer
- Extended Depth of Field (EDOF)
- Extended Dynamic Range (EDR)
- Automatic Magnification Reading (AMR)
- Flexible LED Control (FLC)
- And more...

(*EDOF/EDR only functions under Windows OS)

Working distance/ field of view/ depth of field:

MAGNIFICATION RATE	WORKING DISTANCE *	FIELD OF VIEW(X)	FIELD OF VIEW(Y)	DEPTH OF FIELD
20	60.2	19.5	15.6	2.5
30	33.5	13	10.4	1.8
40	20.9	9.8	7.8	1.5
50	13.9	7.8	6.3	
60	9.7	6.5	5.2	
70	7.1	5.6	4.5	1.0
80	5.5	4.9	3.9	
90	4.5	4.3	3.5	
100	4.1	3.9	3.1	
110	4	3.6	2.8	
120	4.1	3.3	2.6	
130	4.5	3	2.4	
140	5	2.8	2.2	
150	5.6	2.6	2.1	

160	6.3	2.4	2	
170	7.1	2.3	1.8	
180	8	2.2	1.7	
190	8.9	2.1	1.6	
200	9.9	2	1.6	
210	10.9	1.9	1.5	
220	11.9	1.8	1.4	0.1
Listed values may differ slightly	* Without front cap			Unit = mm

Specificatie

Verlichting	
Licht / LED-type	White
Aantal leds	8
LED aan / uit schakelbaar:	Yes
Infrarood filter	IR-afsnijfilter > 650 nm
Diffusor beschikbaar	Yes (N3C-D included)
Emissiefilter	No
Polarisator	Yes, linear
Optiek	
Vergroting	20-220x
Macro zoom	No
Werkafstand	Standard
Type lens	Glas met antireflectiecoating
Sensor	
Sensortype	CMOS
Resolutie	1.3 Megapixel (1280x1024)
Maximale framesnelheid	30 fps
Compatibiliteit	
Interface	USB 2.0
Besturingssysteem	Windows 7, 8, 10 & 11, MacOS 10.11.16 and up
Inbegrepen software	DinoCapture 2.0 (Windows), DinoXcope (Mac OS)
Ondersteunde beeldformaten (Windows)	BMP, GIF, PNG, JPG, TIF, RAS, PNM, TGA, PCX, MNG, WBMP, JP2, JPC, PGX
Ondersteunde videoformaten (Windows)	WMV, FLV, SWF
Ondersteunde	JPEG, PNG

beeldformaten (MacOS)	
Ondersteunde videoformaten (MacOS)	MOV
Beeldvormingsnormen	DirectShow, UVC
Wifi	Wireless-ready, requires the WF-20 adapter (optional)
Behuizing	
Materiaal van de behuizing	Composite/ plastic housing
Afmetingen	11.4cm (L) x 3.3cm (D)
Gewicht	111g
Kabellengte	1.8m
Kenmerken	
Bijzonderheid	Automatic Magnification Reading(AMR), Ext. Dynamic Range (EDR), Extended Depth of Field (EDOF), Flexible LED Control (FLC)
Meting	Yes
Kalibratie	Yes
Microtouch-sensor	Yes
ESD veilig	No
Informatie	
Inhoud van de verpakking	Microscope, Carry pouch, software CD, calibration target, user manual, N3C-O- Open cap, N3C-C- Closed cap, N3C-D- diffuser cap, N3C-E- extension cap, N3C-L- Long cap, N3C-S- Side light cap
Garantie-informatie	2 years European warranty
Regelgevende goedkeuring	CE, FCC, ROHS
Prijsklasse	€700,00 - €800,00

Product galerij

