

AM4117MZT



Merk: Dino-Lite

Productcode: AM4117MZT EDGE PLUS

Korte omschrijving

1.3 Megapixel

10-220x Magnification

Polarizer

Flexible LED Control (FLC)

Robust metal housing

Omschrijving

The Dino-Lite AM4117MZT is part of the EDGE ^{PLUS} series, a special category within the Universal range. It offers a magnification range of 20-220x with 1.3MP and a USB 2.0 connection at 30fps. It offers superb image quality and clarity and color reproduction in a robust, compact and appealing metal housing.



1.3 megapixel
1280 x 1024



USB 2.0



ADJUSTABLE
~10-20x



Measurement
functionality



Polarizer
anti-reflection



Metal
housing



The main features of the AM4117MZT are:

- 1.3 Megapixel EDGE ^{PLUS} sensor
- Flexible LED Control (FLC)
- 10-220x Magnification
- Adjustable polarizer
- 30fps
- Metal housing
- And more...

Working distance/field of view/depth of field

MAGNIFICATION RATE	WORKING DISTANCE*	FIELD OF VIEW(X)	FIELD OF VIEW(Y)	DEPTH OF FIELD
20	59.5	19.5	14.7	5.36
30	32.9	13.0	9.8	2.58
40	20.2	9.8	7.3	1.56
50	13.2	7.8	5.9	1.07
60	9.	6.5	4.9	0.79
70	6.4	5.6	4.2	0.62
80	4.8	4.9	3.7	0.5
90	4	4.3	3.3	0.42
100	3.5	3.9	2.9	0.36
110	3.3	3.6	2.7	0.31
120	3.5	3.3	2.4	0.27
130	3.8	3.0	2.3	0.24
140	4.3	2.8	2.1	0.22
150	4.9	2.6	2.0	0.2
160	5.6	2.4	1.8	0.18
170	6.4	2.3	1.7	0.17
180	7.3	2.2	1.6	0.15
190	8.2	2.1	1.5	0.14
200	9.2	2.0	1.5	0.13
210	10.2	1.9	1.4	0.13
220	11.3	1.8	1.3	0.12

**Listed values
may differ
slightly**

***Without front
cap**

Unit = mm

Specificatie

Verlichting	
Licht / LED-type	White
Aantal leds	8
LED aan / uit schakelbaar:	Yes
Infrarood filter	IR cut-filter >650 nm
Diffusor beschikbaar	Yes (N3C-D included)
Emissiefilter	No
Polarisator	Yes, linear
Optiek	
Vergroting	10-220x
Macro zoom	No
Werkafstand	Standard
Type lens	Glass with anti-reflection coating
Sensor	
Sensortype	CMOS
Resolutie	1.3 Megapixel (1280x1024)
Maximale framesnelheid	30 fps
Compatibiliteit	
Interface	USB 2.0
Besturingssysteem	Windows 7, 8, 10 & 11, MacOS 10.11.6 and up
Inbegrepen software	DinoCapture 2.0 (Windows), DinoXcope (Mac OS)
Ondersteunde beeldformaten (Windows)	BMP, GIF, PNG, JPG, TIF, RAS, PNM, TGA, PCX, MNG, WBMP, JP2, JPC, PGX
Ondersteunde videoformaten (Windows)	WMV, FLV, SWF (max 1.3MP)
Ondersteunde beeldformaten (MacOS)	JPEG, PNG
Ondersteunde videoformaten (MacOS)	MOV
Beeldvormingsnormen	DirectShow, UVC
Wifi	Wireless-ready, requires the WF-10 WiFi streamer (optional)
Behuizing	
Materiaal van de behuizing	Metal housing
Vergrotingsslot	Yes
Afmetingen	10.5cm (L) x 3.2cm (D)

Gewicht	130g
Kabellengte	1.5m
Kenmerken	
Bijzonderheid	Flexible LED Control (FLC)
Meting	Yes
Kalibratie	Yes
Microtouch-sensor	Yes
ESD veilig	Yes
Informatie	
Inhoud van de verpakking	Microscope, Carry pouch, software CD, calibration target, user manual, N3C-O- Open cap, N3C-C- Closed cap, N3C-D- diffuser cap, N3C-E- extension cap, N3C-L- Long cap, N3C-S- Side light cap
Garantie-informatie	2 years European warranty
Regelgevende goedkeuring	CE, FCC, ROHS
Prijsklasse	€900,00 - €1100,00

Product galerij

