

AF4135ZTE



Merk:

Productcode: AF4135ZTE

Korte omschrijving

1.3 Megapixel Edge sensor

10x~330x magnification

Adjustable Polarizer

Flexible LED Control (FLC)

Extensive measurement functionality

Omschrijving

The AF4135ZTE excels with its versatile magnification range of 10x~330x, ensuring detailed exploration across various applications. This model also includes a polarizer, features FLC, and is compatible with the WF-20 Wi-Fi streamer.

In comparison, the AF4x35 series provides a similar working distance range but achieves higher magnifications compared to the AM4x15 series.




USB 2.0



1,3 Megapixels
1280 x 1024



Adjustable
~10-330x



Polarizer
anti-reflection



Measurement
functionality




Flexible LED
Control FLC



Magnification
lock



Standard working
distance



Exchangeable
cap

The AF4135ZTE is equipped with premium features such as Flexible LED control (FLC), integrated polarizer, extensive measurement functionality.

The main features of the AF4135ZTE are:

- Wireless-ready, requires the WF-20 adapter (optional)
- 10x~330x magnification
- 1.3 Megapixel Edge sensor
- Adjustable polarizer
- Flexible LED Control (FLC)
- And more...

Working distance/field of view/depth of field

MAGNIFICATION RATE	WORKING DISTANCE *	FIELD OF VIEW(X)	FIELD OF VIEW(Y)	DEPTH OF FIELD
10	222.3	39.1	29.3	55.5
20	98.9	19.5	14.7	14.6
30	58.5	13.0	9.8	6.8
40	38.7	9.8	7.3	4.0
50	27.2	7.8	5.9	2.7
60	19.9	6.5	4.9	2.0
70	14.9	5.6	4.2	1.5
80	11.5	4.9	3.7	1.2
90	9.0	4.3	3.3	1.0
100	7.2	3.9	2.9	0.8
110	5.9	3.6	2.7	0.7
120	4.9	3.3	2.4	0.6
130	4.3	3.0	2.3	0.5
140	3.9	2.8	2.1	0.5
150	3.7	2.6	2.0	0.4
160	3.6	2.4	1.8	0.4
170	3.7	2.3	1.7	0.4
180	3.8	2.2	1.6	0.3
190	4.1	2.1	1.5	0.3
200	4.4	2.0	1.5	0.3

210	4.7	1.9	1.4	0.3
220	5.2	1.8	1.3	0.2
230	5.6	1.7	1.3	0.2
240	6.2	1.6	1.2	0.2
250	6.7	1.6	1.2	0.2
260	7.3	1.5	1.1	0.2
270	7.9	1.4	1.1	0.2
280	8.5	1.4	1.0	0.2
290	9.2	1.3	1.0	0.2
300	9.9	1.3	1.0	0.2
310	10.6	1.3	0.9	0.2
320	11.3	1.2	0.9	0.1
330	12.0	1.2	0.9	0.1

Specificatie

Verlichting	
Licht / LED-type	White
Aantal leds	8
LED aan / uit schakelbaar:	Yes
Infrarood filter	IR cut-filter >650 nm
Diffusor beschikbaar	Yes (N3C-D included)
Emissiefilter	No
Polarisator	Yes, linear
Optiek	
Magnification	10x~330x
Macro zoom	No
Werkafstand	Standard
Type lens	Glass with anti-reflection coating
Sensor	
Sensortype	CMOS
Resolutie	1.3 Megapixel (1280x1024)
Maximale framesnelheid	30 fps
Compatibiliteit	
Interface	USB 2.0
Besturingssysteem	Windows 7, 8, 10 & 11, MacOS 10.12 and up
Software	DinoCapture 2.0 (Windows), DinoXcope (Mac OS)
Ondersteunde beeldformaten (Windows)	BMP, GIF, PNG, JPG, TIF, RAS, PNM, TGA, PCX, MNG, WBMP, JP2, JPC, PGX
Ondersteunde videoformaten (Windows)	WMV, FLV, SWF
Ondersteunde	JPEG, PNG

beeldformaten (MacOS)	
Ondersteunde videoformaten (MacOS)	MOV
Beeldvormingsnormen	DirectShow, UVC
Wifi	Wireless-ready, requires the WF-20 adapter (optional)
Behuizing	
Materiaal van de behuizing	Composite/ plastic housing
Afmetingen	11.4cm (L) x 3.3cm (D)
Gewicht	111g
Kabellengte	1.8m
Kenmerken	
Bijzonderheid	Flexible LED Control (FLC)
Meting	Yes
Kalibratie	Yes
Microtouch-sensor	Yes
Informatie	
Inhoud van de verpakking	Microscope, Carry pouch, software CD, calibration target, user manual, N3C-O- Open cap, N3C-C- Closed cap, N3C-D- diffuser cap, N3C-E- extension cap, N3C-L- Long cap, N3C-S- Side light cap
Garantie-informatie	2 years European warranty
Regelgevende goedkeuring	CE, FCC, ROHS
Prijsklasse	€550,00 - €750,00