

# AM7115MT-FUW



**Brand:**

**Product Code:** AM7115MT-FUW

## Short Description

5 Megapixel Edge Sensor

Robust metal housing

~375nm + white LEDs

20-220x magnification

Versatility due to exchangeable caps

## Description

The Dino-Lite AM7115MT-FUW is part of the Dino-Lite special light range. This model has two types of LED lights that are switchable between white and UV light. The UV LEDs are near UV LEDs with a spectrum of 375nm. This model offers a standard working distance, a wide magnification range from 20 – 220x and comes with a high quality 5 megapixel Edge sensor.



5 megapixel  
2592 x 1944



USB 2.0



Adjustable  
~20x - 220x



Long working  
distance



Metal  
housing



Flexible LED  
Control FLC



UV-LEDs  
375 nm

Magnification  
lock



Measurement  
functionality



Exchangeable  
cap

## The main features of the AM7115MT-FUW are:


- 5 Megapixel Edge sensor
  - USB 2.0
  - 20-220x magnification
  - Metal housing
  - —
  - N—
  - Extensive measurement functions
  - —
  - Exchangeable front caps
- and more...

## Working distance/field of view/depth of field

MAGNIFICATION RATE	WORKING DISTANCE	FIELD OF VIEW(X)	FIELD OF VIEW(Y)	DEPTH OF FIELD
<b>Listed values may differ slightly</b>		<b>* Without front cap</b>		<b>Unit = mm</b>
20	60.2	19.5	14.6	2.5
30	33.5	13.0	9.7	1.8
40	20.9	9.8	7.3	1.5
50	13.9	7.8	7.8	-
60	9.7	6.5	5.8	-
70	7.1	5.6	4.2	1.0
80	5.5	4.9	3.6	-
90	4.5	4.3	3.2	-
100	4.1	3.9	2.9	-
110	4.0	3.6	2.7	-
120	4.1	3.3	2.4	-
130	4.5	3.0	2.2	-
140	5.0	2.8	2.1	-
150	5.6	2.6	1.9	-

160	6.3	2.4	1.8	-
170	7.1	2.3	1.7	-
180	8.0	2.2	1.6	-
190	8.9	2.1	1.5	-
200	9.9	2.0	1.5	-
210	10.9	1.9	1.4	-
220	11.9	1.8	1.3	-

## Special Light



## Specification

Lighting	
Number of LEDs	~375 nm UV + white
Number of LEDs	4+4
LED on/off switchable:	Yes
Infrared filter	IR cut-filter >650 nm
Diffuser available	Yes (N3C-D included)
Emission filter	Yes, Emission barrier filter 375 nm
Polarizer	No
Optics	
Magnification	20x ~ 220x
Macro zoom	No
Working distance	Standard
Lens type	Glass with anti-reflection coating
Sensor	
Sensor type	CMOS
Resolution	5.0 Megapixel (2592x1944)
Maximum frame rate	30 fps
Compatibility	
Interface	USB 2.0
Operating system	Windows 7, 8, 10 & 11, MacOS 10.9 and up
Software	DinoCapture 2.0 (Windows), DinoXcope (Mac

	OS)
Supported image formats (Windows)	BMP, GIF, PNG, JPG, TIF, RAS, PNM, TGA, PCX, MNG, WBMP, JP2, JPC, PGX
Supported video formats (Windows)	WMV, FLV, SWF
Supported image formats (MacOS)	JPEG, PNG
Supported video formats (MacOS)	MOV (max. 1.3MP)
Imaging standards	DirectShow, UVC
<b>Housing</b>	
Housing material	Metal housing
Magnification lock	Yes
Dimensions	10.5cm (L) x 3.2cm (D)
Weight	140g
Cable length	1.8m
<b>Features</b>	
Special feature	No
Measurement	Yes
Calibration	Yes
Microtouch sensor	Yes
ESD safe	Yes
<b>Information</b>	
Package contents	Microscope, carry pouch, software CD, calibration target, user manual, Microscope, carry pouch, software CD, calibration target, user manual, N3C-C (Close Cap) N3C-EB (Extended Open Black Cap) N3C-L (Long Cap) N3C-OB (Black Open Cap) N3C-S (Sidelight Cap)
Warranty information	2 years European warranty
Regulatory approval	CE, FCC, ROHS
Price range	€900,00 - €1100,00