Dino-Lite Europe - Phone: - Email:

### AM4917MZT



Ürün Kodu: AM4917MZT EDGE PLUS

### **Short Description**

1.3 Megapixel
10-220x Magnification
Polarizer
Flexible LED Control (FLC)
Automatic Magnification Reading (AMR)
EDOF/EDR & Depth information
Robust metal housing

### Aç?klama

The Dino-Lite AM4917MZT is part of the EDGE PLUS series, a special category within the Universal range. It offers a magnification range of 10-220x with 1.3MP and a USB 2.0 connection at 30fps. It offers superb image quality and clarity and color reproduction in a robust, compact and appealing metal housing.

A unique feature within the EDGE <sup>PLUS</sup> series for the AM4917MZT model is the possibility to acquire Depth Information. By indicating the variations in focus shifts, you can obtain depth information of grooves, holes, and other types of topographical variations. Please click <u>here</u> for the manual on "how to acquire depth information with the AM4917-models".



EDOF allows users to automatically capture multiple images at different depths and automatically combine them into one clear image. EDR automatically captures and combines multiple images at different exposure levels to produce a final image with greater dynamic range. The AMR function automatically detects and displays the magnification of the Dino-Lite. The magnification is displayed within the Dino-Lite software and stored with the captured picture and simplifies the measuring process. Because of the built-in polarization filter this model is ideal when working with shiny or reflective objects such as metal, plastic, glass, jewelry, electronics, etc.

#### The main features of the AM4917MZT are:

- Automatic Magnification Reading (AMR)
- 1.3 Megapixel EDGE PLUS sensor
- Flexible LED Control (FLC)
- Extended Depth of Field (EDOF)
- Extended Dynamic Range (EDR)
- 10-220x Magnification
- Adjustable polarizer
- 30fps
- Metal housing
- And more...

## Working distance/field of view/depth of field

MAGNIFICAT	IWORKING	FIELD OF	FIELD OF	<b>DEPTH OF</b>
ON RATE	<b>DISTANCE*</b>	VIEW(X)	VIEW(Y)	FIELD
20	59.5	19.5	14.7	5.36
30	32.9	13.0	9.8	2.58
40	20.2	9.8	7.3	1.56
50	13.2	7.8	5.9	1.07
60	9	6.5	4.9	0.79
70	6.4	5.6	4.2	0.62
80	4.8	4.9	3.7	0.5
90	4	4.3	3.3	0.42
100	3.5	3.9	2.9	0.36
110	3.3	3.6	2.7	0.31
120	3.5	3.3	2.4	0.27
130	3.8	3.0	2.3	0.24
140	4.3	2.8	2.1	0.22
150	4.9	2.6	2.0	0.2
160	5.6	2.4	1.8	0.18
170	6.4	2.3	1.7	0.17
180	7.3	2.2	1.6	0.15
190	8.2	2.1	1.5	0.14
200	9.2	2.0	1.5	0.13
210	10.2	1.9	1.4	0.13
220	11.3	1.8	1.3	0.12
Listed values	*Without front			Unit = mm
may differ slightly	cap			

## Özellikler

Lighting	
Light/ LED type	White
Number of LEDs	8
LED on/off switchable:	Yes
Infrared filter	IR cut-filter >650 nm
Diffuser available	Yes (N3C-D included)
Emission filter	No
Polarizer	Yes, linear
Optics	

Magnification	$10x \sim 220x$			
Macro zoom	No			
Working distance	Standard			
Lens type	Glass with anti-reflection coating			
Sensor				
Sensor type	CMOS			
Resolution	1.3 Megapixel (1280x1024)			
Maximum frame rate	30 fps			
Compatibility				
Interface	USB 2.0			
Operating system	Windows 7, 8, 10 & 11, MacOS 11.1 and up			
Software	DinoCapture 2.0 (Windows), DinoXcope (Mac OS)			
Supported image formats	BMP, GIF, PNG, JPG, TIF, RAS, PNM, TGA,			
(Windows)	PCX, MNG, WBMP, JP2, JPC, PGX			
Supported video formats	WMV, FLV, SWF (max 1.3MP)			
(Windows)				
Supported image formats	JPEG, PNG			
(MacOS)				
Supported video formats	MOV			
(MacOS)				
Imaging standards	DirectShow, UVC			
Wifi	Wireless-ready, requires the WF-10 WiFi streamer			
	(optional)			
Housing				
Housing material	Metal housing			
Magnification lock	Yes			
Dimensions	10.5cm (L) x 3.2cm (D)			
Weight	130g			
Cable length	1.5m			
Features				
Special feature	Automatic Magnification Reading (AMR),			
	Extended Dynamic Range (EDR), Extended Depth			
	of Field (EDOF), Flexible LED Control(FLC)			
Measurement	Yes			
Calibration	Yes			
Microtouch sensor	Yes			
ESD safe	Yes			
Information				
Package contents	Microscope, carry pouch, software CD, calibration target, user manual, N3C-O- Open cap, N3C-C-Closed cap, N3C-D- diffuser cap, N3c-E-extension			

	cap, N3C-L- Long cap, N3C-S- Side light cap
Warranty information	2 years European warranty
Regulatory approval	CE, FCC, ROHS
Price range	€1100,00 - €1300,00

# **Product Gallery**





